

Измеритель плотности клеток Ultrospec 30

Технические характеристики

По вопросам продаж и поддержки обращайтесь:

Алматы (727)345-47-04
Ангарск (3955)60-70-56
Архангельск (8182)63-90-72
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Благовещенск (4162)22-76-07
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Владикавказ (8672)28-90-48
Владимир (4922)49-43-18
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Коломна (4966)23-41-49
Кострома (4942)77-07-48
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Курган (3522)50-90-47
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Ноябрьск (3496)41-32-12
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Петрозаводск (8142)55-98-37
Псков (8112)59-10-37
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Саранск (8342)22-96-24
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Сургут (3462)77-98-35
Сыктывкар (8212)25-95-17
Тамбов (4752)50-40-97
Тверь (4822)63-31-35

Тольятти (8482)63-91-07
Томск (3822)98-41-53
Тула (4872)33-79-87
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Улан-Удэ (3012)59-97-51
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Чебоксары (8352)28-53-07
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Чита (3022)38-34-83
Якутск (4112)23-90-97
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +7(727)345-47-04

Беларусь +(375)257-127-884

Узбекистан +998(71)205-18-59

Киргизия +996(312)96-26-47

эл.почта: bmq@nt-rt.ru || сайт: <https://biochrom.nt-rt.ru/>



Biochrom Ultraspec 30 Cell Density Meter

Compact, portable, easy-to-use cell density meter

Applications

Suitable for:

- Performing microbial growth phase analysis in bacterial and yeast cell suspensions
- Bacterial transformation
- Plasmid amplification
- Antibiotic studies
- Quality control
- Contaminant detection
- Precision fermentation
- Cell growth assays

Key Features

- **Creation of Standard Curves**
Generate and save cell and condition specific standard curves using absorbance values or McFarland standards to use for future quantification.
- **Compact and Portable**
Hand-held instrument with rechargeable battery for easy movement around the lab
- **Touchscreen Display**
Intuitive menu arrangement easily navigated using the colour touchscreen.
- **Instrument Data Output**
Measurement data can be exported to a USB flash drive as common-separated value (.csv).

Technical Specifications

Part Number	80-3008-01
Wavelength Range	600 nm
Light Source	LED
Detector	Photo Diode
Display	4.3-inch, 480 x 272-pixel resolution backlit LCD colour display
Storage Conditions	-10° C to 70° C (14° F to 158° F)
Spectral Bandwidth	40nm
Photometric Range	Absorbance 0.3 to 2.0A
Photometric Accuracy	< ± 0.05A 1A using neutral density filter
Photometric Repeatability	± 0.02A at 1A om 10mm cuvette
Sample Holder	Accepts: <ul style="list-style-type: none"> • 10mm x 10mm cuvettes • 16mm test tubes Can accept 10-12mm tubes with optional adapter
Data Connector: USB-A	Interface for memory device
Power Connector: USB-C	Input power at 5V, 2 Amp max
Power (via external charger)	USB charger specifications (included): 100-240V, 50/60Hz, 10W
Battery	Internal rechargeable Li-Ion battery
Compliance	CE & UKCA marked, US/CAN safety (ETL or equivalent)
Dimensions	170mm W x 210 D x 50 mm H
Weight	0.6 kg (1.3 lbs)

Ordering Information

Ultrospec 30 Cell Density Meter <i>(Includes: Instrument, power supply, USB cable, 1 pack of x8 cuvettes, Quick Start Guide and QR code with link to User Manual)</i>	80-3008-01
--	------------

Accessories

User Replaceable Battery	80-3007-99
USB-C Cable	80-3008-08
Power Supply	80-3008-09
Pack of 100 disposable cells, 1ml min. volume	80-2004-53
Adapter set for 10 and 12 mm tubes	80-3000-57

По вопросам продаж и поддержки обращайтесь:

Алматы (727)345-47-04
Ангарск (3955)60-70-56
Архангельск (8182)63-90-72
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Благовещенск (4162)22-76-07
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Владикавказ (8672)28-90-48
Владимир (4922)49-43-18
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Коломна (4966)23-41-49
Кострома (4942)77-07-48
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Курган (3522)50-90-47
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Ноябрьск (3496)41-32-12
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Петрозаводск (8142)55-98-37
Псков (8112)59-10-37
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Саранск (8342)22-96-24
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Сургут (3462)77-98-35
Сыктывкар (8212)25-95-17
Тамбов (4752)50-40-97
Тверь (4822)63-31-35

Тольятти (8482)63-91-07
Томск (3822)98-41-53
Тула (4872)33-79-87
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Улан-Удэ (3012)59-97-51
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Чебоксары (8352)28-53-07
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Чита (3022)38-34-83
Якутск (4112)23-90-97
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +7(727)345-47-04

Беларусь +(375)257-127-884

Узбекистан +998(71)205-18-59

Киргизия +996(312)96-26-47

эл.почта: bmq@nt-rt.ru || сайт: <https://biochrom.nt-rt.ru/>